

# Technical data sheet



## Product features

### Bain marie electric 2x GN 1/1 - 150 counter top

<b>Model</b>	<b>SAP Code</b>	00000059
--------------	-----------------	----------



- Drain: No
- Material: Stainless steel
- Protection of controls: IPX4
- Maximum device temperature [°C]: 90

<b>SAP Code</b>	00000059	<b>Power electric [kW]</b>	3.000
<b>Net Width [mm]</b>	660	<b>Loading</b>	230 V / 1N - 50 Hz
<b>Net Depth [mm]</b>	535	<b>Number of GN / EN</b>	2
<b>Net Height [mm]</b>	229	<b>GN / EN size in device</b>	GN 1/1
<b>Net Weight [kg]</b>	17.00	<b>GN device depth</b>	150

# Technical data sheet






Technical drawing

Bain marie electric 2x GN 1/1 - 150 counter top

Model

SAP Code

00000059



# Technical data sheet



## Product benefits

### Bain marie electric 2x GN 1/1 - 150 counter top

Model

SAP Code

00000059

1

#### All-stainless design

long life  
resistance of AISI 304 stainless steel material  
the material does not cut

- savings on service interventions
- easy cleaning and maintenance of equipment

2

#### Degree of protection of the control elements IPX4

maintenance-free system  
resistance to splash water  
long life

- savings on service interventions
- easy cleaning and maintenance of equipment

3

#### Easy manipulation

easy portability

- flexibility in the kitchen, can be used for banquets

# Technical data sheet



## Technical parameters

### Bain marie electric 2x GN 1/1 - 150 counter top

Model

SAP Code

00000059

**1. SAP Code:**

00000059

**2. Net Width [mm]:**

660

**3. Net Depth [mm]:**

535

**4. Net Height [mm]:**

229

**5. Net Weight [kg]:**

17.00

**6. Gross Width [mm]:**

580

**7. Gross depth [mm]:**

700

**8. Gross Height [mm]:**

240

**9. Gross Weight [kg]:**

19.00

**10. Device type:**

Electric unit

**11. Construction type of device:**

Table top

**12. Power electric [kW]:**

3.000

**13. Loading:**

230 V / 1N - 50 Hz

**14. Protection of controls:**

IPX4

**15. Material:**

Stainless steel

**16. Indicators:**

operation and warm-up

**17. Maximum device temperature [°C]:**

90

**18. Minimum device temperature [°C]:**

30

**19. Drain:**

No

**20. Number of GN / EN:**

2

**21. GN / EN size in device:**

GN 1/1

**22. GN device depth:**

150

**23. Heating location:**

Under the bottom of the bathtub